


TEC FLEX Low & High Power IP00

Linjär LED moduler för flexibla och individuella belysningslösningar



Produktegenskaper

- Flexibel klippbar LED list
- Available with color temperature: 2,700K, 3,000 K, 4,000 K
- Up to 50,000 h lifetime @ tc max
- Color consistency in 3 SDCM

Produktfördelar

- Enkel montering på många släta ytor tack vare självhäftande tejp på baksidan



Tekniska data

Elektriska data

Produktbeskrivning	Nominell märkspänning	Strömtyp	Märkeffekt	Inspänningso mråde	Accidental reverse input voltage protection up to
TF300-G1 -827-05	240 V	Direkt ström (DC)	1400 W	23...25 V	25 V
TF300-G1 -830-05	240 V	Direkt ström (DC)	1400 W	23...25 V	25 V
TF300-G1 -840-05	240 V	Direkt ström (DC)	1400 W	23...25 V	25 V
TF300-G1 -850-05	240 V	Direkt ström (DC)	1400 W	23...25 V	25 V
TF300-G1 -865-05	240 V	Direkt ström (DC)	1400 W	23...25 V	25 V
TF1000-G1 -827-05	240 V	Direkt ström (DC)	4750 W	23...25 V	25 V
TF1000-G1 -830-05	240 V	Direkt ström (DC)	4750 W	23...25 V	25 V
TF1000-G1 -840-05	240 V	Direkt ström (DC)	4750 W	23...25 V	25 V
TF1000-G1 -865-05	240 V	Direkt ström (DC)	4750 W	23...25 V	25 V
TF1000-G1 -850-05	240 V	Direkt ström (DC)	4750 W	23...25 V	25 V
TF2000-G1 -827-05	240 V	Direkt ström (DC)	7750 W	23...25 V	25 V
TF2000-G1 -830-05	240 V	Direkt ström (DC)	7750 W	23...25 V	25 V
TF2000-G1 -840-05	240 V	Direkt ström (DC)	7750 W	23...25 V	25 V
TF2000-G1 -865-05	240 V	Direkt ström (DC)	7750 W	23...25 V	25 V
TF2000-G1 -850-05	240 V	Direkt ström (DC)	7750 W	23...25 V	25 V


Fotometrisk data

Produktbeskrivning	Ljuskfärg LED	Färgåtergivningsindex Ra	Ljuskfärg (angiven)
TF300-G1 -827-05	vit	80	Vit
TF300-G1 -830-05	vit	80	Vit
TF300-G1 -840-05	vit	80	Vit
TF300-G1 -850-05	vit	80	Vit
TF300-G1 -865-05	vit	80	Vit
TF1000-G1 -827-05	vit	80	Vit
TF1000-G1 -830-05	vit	80	Vit
TF1000-G1 -840-05	vit	80	Vit
TF1000-G1 -865-05	vit	80	Vit
TF1000-G1 -850-05	vit	80	Vit
TF2000-G1 -827-05	vit	80	Vit
TF2000-G1 -830-05	vit	80	Vit
TF2000-G1 -840-05	vit	80	Vit
TF2000-G1 -865-05	vit	80	Vit
TF2000-G1 -850-05	vit	80	Vit

Mått

Produktbeskrivning	Längd	produktvikt
TF300-G1 -827-05	50000 mm	6000 g
TF300-G1 -830-05	50000 mm	6000 g
TF300-G1 -840-05	50000 mm	6000 g
TF300-G1 -850-05	50000 mm	6000 g
TF300-G1 -865-05	50000 mm	6000 g
TF1000-G1 -827-05	50000 mm	6000 g
TF1000-G1 -830-05	50000 mm	6000 g
TF1000-G1 -840-05	50000 mm	6000 g
TF1000-G1 -865-05	50000 mm	6000 g
TF1000-G1 -850-05	50000 mm	6000 g
TF2000-G1 -827-05	50000 mm	6400 g
TF2000-G1 -830-05	50000 mm	6400 g
TF2000-G1 -840-05	50000 mm	6400 g
TF2000-G1 -865-05	50000 mm	6400 g
TF2000-G1 -850-05	50000 mm	6400 g

Produktskiss med nummer



TF300-G1 -827-05, TF300-G1 -830-05, TF300-G1 -840-05,
TF300-G1 -850-05, TF300-G1 -865-05, TF1000-G1 -827-05,
TF1000-G1 -830-05, TF1000-G1 -840-05, TF1000-G1 -865-
05, TF1000-G1 -850-05, TF2000-G1 -827-05, TF2000-G1 -
830-05, TF2000-G1 -840-05, TF2000-G1 -865-05, TF2000-
G1 -850-05

Temperaturer och driftsförhållanden

Produktbeskrivning	Temperaturområde vid Tc punkten	Förvaringstemperatur
TF300-G1 -827-05	-25...80 °C	-30...85 °C
TF300-G1 -830-05	-25...80 °C	-30...85 °C
TF300-G1 -840-05	-25...80 °C	-30...85 °C
TF300-G1 -850-05	-25...80 °C	-30...85 °C
TF300-G1 -865-05	-25...80 °C	-30...85 °C
TF1000-G1 -827-05	-25...80 °C	-30...85 °C
TF1000-G1 -830-05	-25...80 °C	-30...85 °C
TF1000-G1 -840-05	-25...80 °C	-30...85 °C
TF1000-G1 -865-05	-25...80 °C	-30...85 °C
TF1000-G1 -850-05	-25...80 °C	-30...85 °C
TF2000-G1 -827-05	-25...80 °C	-30...85 °C
TF2000-G1 -830-05	-25...80 °C	-30...85 °C
TF2000-G1 -840-05	-25...80 °C	-30...85 °C
TF2000-G1 -865-05	-25...80 °C	-30...85 °C
TF2000-G1 -850-05	-25...80 °C	-30...85 °C

Tillägg produktdata

Produktbeskrivning	Produkten ersätts av EAN	ID of contained light source [AGGR]
TF300-G1 -827-05	4052899527874, 4052899527959	LS_SHZ_600301
TF300-G1 -830-05	4052899527898, 4052899527973	LS_SHZ_600302
TF300-G1 -840-05	4052899527911, 4052899527997	LS_SHZ_600303
TF300-G1 -850-05		LS_SHZ_600304
TF300-G1 -865-05	4052899527935, 4052899528017	LS_SHZ_600305
TF1000-G1 -827-05	4052899525894	LS_SHZ_600306
TF1000-G1 -830-05	4052899525917	LS_SHZ_600307
TF1000-G1 -840-05	4052899525931	LS_SHZ_600308
TF1000-G1 -865-05	4052899525955	LS_SHZ_600310
TF1000-G1 -850-05		LS_SHZ_600309
TF2000-G1 -827-05	4052899528956	LS_SHZ_600297
TF2000-G1 -830-05	4052899528970	LS_SHZ_600311
TF2000-G1 -840-05	4052899528994	LS_SHZ_600312
TF2000-G1 -865-05	4052899529014	LS_SHZ_600314
TF2000-G1 -850-05		LS_SHZ_600313

Certifikat och Standarder

Produktbeskrivning	Standarder	Energy efficiency class of the contained light source
TF300-G1 -827-05	CE/EAC/ENEC	E
TF300-G1 -830-05	CE/EAC/ENEC	E
TF300-G1 -840-05	CE/EAC/ENEC	E
TF300-G1 -850-05	CE/EAC/ENEC	E
TF300-G1 -865-05	CE/EAC/ENEC	E
TF1000-G1 -827-05	CE/EAC/ENEC	F
TF1000-G1 -830-05	CE/EAC/ENEC	E
TF1000-G1 -840-05	CE/EAC/ENEC	E
TF1000-G1 -865-05	CE/EAC/ENEC	E
TF1000-G1 -850-05	CE/EAC/ENEC	E
TF2000-G1 -827-05	CE/EAC/ENEC	F
TF2000-G1 -830-05	CE/EAC/ENEC	E
TF2000-G1 -840-05	CE/EAC/ENEC	E
TF2000-G1 -865-05	CE/EAC/ENEC	E
TF2000-G1 -850-05	CE/EAC/ENEC	E

Logistikdata

Produktbeskrivning	Statistiskt varunummer
TF300-G1 -827-05	85395100000
TF300-G1 -830-05	85395100000
TF300-G1 -840-05	85395100000
TF300-G1 -850-05	85395100000
TF300-G1 -865-05	85395100000
TF1000-G1 -827-05	85395100000
TF1000-G1 -830-05	85395100000
TF1000-G1 -840-05	85395100000
TF1000-G1 -865-05	85395100000
TF1000-G1 -850-05	85395100000
TF2000-G1 -827-05	85395100000
TF2000-G1 -830-05	85395100000
TF2000-G1 -840-05	85395100000
TF2000-G1 -865-05	85395100000
TF2000-G1 -850-05	85395100000

Environmental information
Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)

Produktbeskrivning	Date of Declaration	Primary Article Identifier	Candidate List Substance 1
TF300-G1 -827-05	16-06-2023	4062172107020	Lead
TF300-G1 -830-05	11-04-2023	4062172107044	No declarable substances contained
TF300-G1 -840-05	11-04-2023	4062172107068	No declarable substances contained
TF300-G1 -850-05	11-04-2023	4062172107082	No declarable substances contained
TF300-G1 -865-05	11-04-2023	4062172107105	No declarable substances contained
TF1000-G1 -827-05	07-07-2023	4062172107129	Lead
TF1000-G1 -830-05	07-07-2023	4062172107143	Lead
TF1000-G1 -840-05	07-07-2023	4062172107167	Lead
TF1000-G1 -865-05	07-07-2023	4062172107204	Lead
TF1000-G1 -850-05	07-07-2023	4062172107181	Lead
TF2000-G1 -827-05	07-07-2023	4062172107228	Lead
TF2000-G1 -830-05	28-04-2023	4062172107242	Lead
TF2000-G1 -840-05	07-07-2023	4062172107266	Lead
TF2000-G1 -865-05	07-07-2023	4062172107303	Lead
TF2000-G1 -850-05	07-07-2023	4062172107280	Lead

Produktbeskrivning	CAS No. of substance 1	Safe Use Instruction	Declaration No. in SCIP database
TF300-G1 -827-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	9133cea5-6410-4a59-aa22-2a2ffc992bb4
TF300-G1 -830-05			No declarable substances contained
TF300-G1 -840-05			No declarable substances contained
TF300-G1 -850-05			No declarable substances contained
TF300-G1 -865-05			No declarable substances contained
TF1000-G1 -827-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	0d45c291-edf3-4f37-807a-b4632b7e32ef
TF1000-G1 -830-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	f47ddd96-2f0c-4be0-b9f3-67b340379d83
TF1000-G1 -840-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	f5b78ec7-647f-454a-901a-4fb4ffd026af

Datablad produktfamilj

Produktbeskrivning	CAS No. of substance 1	Safe Use Instruction	Declaration No. in SCIP database
TF1000-G1 -865-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	9b1283b1-d929-4488-b6ec-9040a3357458
TF1000-G1 -850-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	9742bd4b-148f-415d-a5b8-86454badd42b
TF2000-G1 -827-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	d9920b58-1cd8-421d-aeb4-fa2537f6dce1
TF2000-G1 -830-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	789055d4-3976-4e52-bc3c-aff122903ffc
TF2000-G1 -840-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	85b0066b-1c51-402f-b091-99c5dd464158
TF2000-G1 -865-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	73e72f9a-2287-4087-a748-2e363af4c5cd
TF2000-G1 -850-05	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	ea7f5fd5-7b2f-4c21-9548-ae4d691cfa6a

Teknisk utrustning

– Förenklad anslutning med matchande tillvals CONNECTsystem

Applikationsråd

För mer detaljerad applikationsinformation och grafik, vänligen se produktdatablad

Försäljning och teknisk support

Försäljning och teknisk support www.osram.se

Download

Dokument	
	User instruction TEC Flex IP00

Datablad produktfamilj

	Product Datasheet TEC Flex IP00 Product Datasheet (EN)
	Broschyrer Light is strong - Discover the versatile and flexible lighting system OSRAM 24V TEC Flex (EN)
	Certifikat TFX ENEC 130520
	Konformitetsdeklaration TECFlex CE 4210017 080823
	CAD-data DWG TEC Flex and TEC Flex Shortpitch
	Eulumdat EULUMDAT Tec Flex IP00
	Eulumdat TF300-G1-827 LTD 130122
	IES data TF300-G1-827 IES 130122
	Eulumdat TF300-G1-830 LTD 130122
	IES data TF300-G1-830 IES 130122
	Eulumdat TF300-G1-840 LTD 130122
	IES data TF300-G1-840 IES 130122
	Eulumdat TF300-G1-850 LTD 130122
	IES data TF300-G1-850 IES 130122
	Eulumdat TF300-G1-865 LTD 130122
	IES data TF300-G1-865 IES 130122
	Eulumdat TF1000-G1-827 LTD 130122
	IES data TF1000-G1-827 IES 130122
	Eulumdat TF1000-G1-830 LTD 130122
	IES data TF1000-G1-830 IES 130122
	Eulumdat TF1000-G1-840 LTD 130122
	IES data TF1000-G1-840 IES 130122
	Eulumdat TF1000-G1-865 LTD 130122

Datablad produktfamilj

	IES data TF1000-G1-865 IES 130122
	Eulumdat TF1000-G1-850 LTD 130122
	IES data TF1000-G1-850 IES 130122
	Eulumdat TF2000-G1-827 LTD 130122
	IES data TF2000-G1-827 IES 130122
	Eulumdat TF2000-G1-830 LTD 130122
	IES data TF2000-G1-830 IES 130122
	Eulumdat TF2000-G1-840 LTD 130122
	IES data TF2000-G1-840 IES 130122
	Eulumdat TF2000-G1-865 LTD 130122
	IES data TF2000-G1-865 IES 130122
	Eulumdat TF2000-G1-850 LTD 130122
	IES data TF2000-G1-850 IES 130122

Ecodesign regulation information:

- This product is considered to be a "containing product" in the sense of Regulations (EU) 2019/2020 and (EU) 2019/2015.
- Tolerances of the reported values, are according to LED Modules Performance standard IEC/EN 62717.
- In general, the replacement of the contained light sources without permanent damage to the product with the use of common available tools is possible in the final application when they can be dismantled from the installation environment and substituted for the necessary number of light sources restoring its full electrical/mechanical/thermal/optical functionality by means of a professional installer. In the contrary, and limited to the LINEARlight Flex Diffuse, LINEARlight Rigid Finesse, GINO LED Flex Diffuse and LUMINENT Milky product families, the contained light source is an integrated part of the containing product and its removal can only be done by causing a permanent damage to the containing product due to its tight mechanical, electrical, optical, thermal interaction and/or environmental protection with or from the containing product. Therefore, a replacement of the light source with the use of common available tools is not justified.
- Dismantling of light sources from containing products at end of life: Containing products with light sources which are scalable in length can be cut to the length of the contained light source and if applicable mechanically detached from protective and/or optical covers. Containing products shall be separated from building material and/or from other additional mounting accessories by means of a professional installer. Separate control gear and light sources must be disposed of at certified disposal companies in accordance with Directive 2012/19/EU (WEEE) in the EU and with Waste Electrical and Electronic Equipment (WEEE) Regulations 2013 in the UK. For this purpose, collection points for recycling centres and take-back systems (CRSO) are available from retailers or private disposal companies, which accept separate control gear and light sources free of charge. In this way, raw materials are conserved and materials are recycled.

Logistiska data

Produktnummer	Produktbeskrivning	Förpackningsenhet (Styck/Enhet)	Dimensioner (längd x bredd x höjd)	Volym	Bruttovikt
4062172107020	TF300-G1 -827-05	Transportförpackning 10	225 mm x 240 mm x 120 mm	6.48 dm ³	1254.00 g
4062172107044	TF300-G1 -830-05	Transportförpackning 10	225 mm x 240 mm x 120 mm	6.48 dm ³	1254.00 g
4062172107068	TF300-G1 -840-05	Transportförpackning 10	225 mm x 240 mm x 120 mm	6.48 dm ³	1254.00 g
4062172107082	TF300-G1 -850-05	Transportförpackning 10	225 mm x 240 mm x 120 mm	6.48 dm ³	1254.00 g
4062172107105	TF300-G1 -865-05	Transportförpackning 10	225 mm x 240 mm x 120 mm	6.48 dm ³	1254.00 g
4062172107129	TF1000-G1 -827-05	Transportförpackning 10	225 mm x 240 mm x 120 mm	6.48 dm ³	1254.00 g
4062172107143	TF1000-G1 -830-05	Transportförpackning 10	225 mm x 240 mm x 120 mm	6.48 dm ³	1254.00 g
4062172107167	TF1000-G1 -840-05	Transportförpackning 10	225 mm x 240 mm x 120 mm	6.48 dm ³	1254.00 g
4062172107204	TF1000-G1 -865-05	Transportförpackning 10	225 mm x 240 mm x 120 mm	6.48 dm ³	1254.00 g
4062172107181	TF1000-G1 -850-05	Transportförpackning 10	225 mm x 240 mm x 120 mm	6.48 dm ³	1254.00 g
4062172107228	TF2000-G1 -827-05	Transportförpackning 10	225 mm x 240 mm x 120 mm	6.48 dm ³	1294.00 g

Datablad produktfamilj

Logistiska data

4062172107242	TF2000-G1 -830-05	Transportförpackning 10	225 mm x 240 mm x 120 mm	6.48 dm ³	1294.00 g
4062172107266	TF2000-G1 -840-05	Transportförpackning 10	225 mm x 240 mm x 120 mm	6.48 dm ³	1294.00 g
4062172107303	TF2000-G1 -865-05	Transportförpackning 10	225 mm x 240 mm x 120 mm	6.48 dm ³	1294.00 g
4062172107280	TF2000-G1 -850-05	Transportförpackning 10	225 mm x 240 mm x 120 mm	6.48 dm ³	1294.00 g

Produktkoden gäller minsta tillåtna beställningskvantitet. En transportförpackning kan innehålla en eller flera produkter. Vid orderläggning, vänligen ange en eller flera transportförpackningar.

Valfria tillbehör

Produktbeskrivning	Tillbehörets namn	Tillbehörets kod
TF300-G1 -827-05	CONN-FLEX -2P-050 KIT 10PCS	▶ 4062172179591
TF300-G1 -827-05	CONN-FLEX -2P-200 KIT 10PCS	▶ 4062172179614
TF300-G1 -827-05	CORNER-FLEX -4P-003 KIT 10PCS	▶ 4062172179638
TF300-G1 -827-05	CORNER-FLEX -4P-015 KIT 10PCS	▶ 4062172179676
TF300-G1 -827-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TF300-G1 -827-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TF300-G1 -827-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TF300-G1 -827-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TF300-G1 -827-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TF300-G1 -830-05	CONN-FLEX -2P-050 KIT 10PCS	▶ 4062172179591
TF300-G1 -830-05	CONN-FLEX -2P-200 KIT 10PCS	▶ 4062172179614
TF300-G1 -830-05	CORNER-FLEX -4P-003 KIT 10PCS	▶ 4062172179638
TF300-G1 -830-05	CORNER-FLEX -4P-015 KIT 10PCS	▶ 4062172179676
TF300-G1 -830-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TF300-G1 -830-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TF300-G1 -830-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TF300-G1 -830-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TF300-G1 -830-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TF300-G1 -840-05	CONN-FLEX -2P-050 KIT 10PCS	▶ 4062172179591
TF300-G1 -840-05	CONN-FLEX -2P-200 KIT 10PCS	▶ 4062172179614
TF300-G1 -840-05	CORNER-FLEX -4P-003 KIT 10PCS	▶ 4062172179638
TF300-G1 -840-05	CORNER-FLEX -4P-015 KIT 10PCS	▶ 4062172179676

Datablad produktfamilj

TF300-G1 -840-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TF300-G1 -840-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TF300-G1 -840-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TF300-G1 -840-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TF300-G1 -840-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TF300-G1 -850-05	CONN-FLEX -2P-050 KIT 10PCS	▶ 4062172179591
TF300-G1 -850-05	CONN-FLEX -2P-200 KIT 10PCS	▶ 4062172179614
TF300-G1 -850-05	CORNER-FLEX -4P-003 KIT 10PCS	▶ 4062172179638
TF300-G1 -850-05	CORNER-FLEX -4P-015 KIT 10PCS	▶ 4062172179676
TF300-G1 -850-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TF300-G1 -850-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TF300-G1 -850-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TF300-G1 -850-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TF300-G1 -850-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TF300-G1 -865-05	CONN-FLEX -2P-050 KIT 10PCS	▶ 4062172179591
TF300-G1 -865-05	CONN-FLEX -2P-200 KIT 10PCS	▶ 4062172179614
TF300-G1 -865-05	CORNER-FLEX -4P-003 KIT 10PCS	▶ 4062172179638
TF300-G1 -865-05	CORNER-FLEX -4P-015 KIT 10PCS	▶ 4062172179676
TF300-G1 -865-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TF300-G1 -865-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TF300-G1 -865-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TF300-G1 -865-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TF300-G1 -865-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TF1000-G1 -827-05	CONN-FLEX -2P-050 KIT 10PCS	▶ 4062172179591
TF1000-G1 -827-05	CONN-FLEX -2P-200 KIT 10PCS	▶ 4062172179614
TF1000-G1 -827-05	CORNER-FLEX -4P-003 KIT 10PCS	▶ 4062172179638
TF1000-G1 -827-05	CORNER-FLEX -4P-015 KIT 10PCS	▶ 4062172179676
TF1000-G1 -827-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TF1000-G1 -827-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TF1000-G1 -827-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TF1000-G1 -827-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TF1000-G1 -827-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TF1000-G1 -830-05	CONN-FLEX -2P-050 KIT 10PCS	▶ 4062172179591
TF1000-G1 -830-05	CONN-FLEX -2P-200 KIT 10PCS	▶ 4062172179614
TF1000-G1 -830-05	CORNER-FLEX -4P-003 KIT 10PCS	▶ 4062172179638
TF1000-G1 -830-05	CORNER-FLEX -4P-015 KIT 10PCS	▶ 4062172179676
TF1000-G1 -830-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TF1000-G1 -830-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889

Datablad produktfamilj

TF1000-G1 -830-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TF1000-G1 -830-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TF1000-G1 -830-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TF1000-G1 -840-05	CONN-FLEX -2P-050 KIT 10PCS	▶ 4062172179591
TF1000-G1 -840-05	CONN-FLEX -2P-200 KIT 10PCS	▶ 4062172179614
TF1000-G1 -840-05	CORNER-FLEX -4P-003 KIT 10PCS	▶ 4062172179638
TF1000-G1 -840-05	CORNER-FLEX -4P-015 KIT 10PCS	▶ 4062172179676
TF1000-G1 -840-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TF1000-G1 -840-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TF1000-G1 -840-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TF1000-G1 -840-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TF1000-G1 -840-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TF1000-G1 -865-05	CONN-FLEX -2P-050 KIT 10PCS	▶ 4062172179591
TF1000-G1 -865-05	CONN-FLEX -2P-200 KIT 10PCS	▶ 4062172179614
TF1000-G1 -865-05	CORNER-FLEX -4P-003 KIT 10PCS	▶ 4062172179638
TF1000-G1 -865-05	CORNER-FLEX -4P-015 KIT 10PCS	▶ 4062172179676
TF1000-G1 -865-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TF1000-G1 -865-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TF1000-G1 -865-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TF1000-G1 -865-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TF1000-G1 -865-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TF1000-G1 -850-05	CONN-FLEX -2P-050 KIT 10PCS	▶ 4062172179591
TF1000-G1 -850-05	CONN-FLEX -2P-200 KIT 10PCS	▶ 4062172179614
TF1000-G1 -850-05	CORNER-FLEX -4P-003 KIT 10PCS	▶ 4062172179638
TF1000-G1 -850-05	CORNER-FLEX -4P-015 KIT 10PCS	▶ 4062172179676
TF1000-G1 -850-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TF1000-G1 -850-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TF1000-G1 -850-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TF1000-G1 -850-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TF1000-G1 -850-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TF2000-G1 -827-05	CONN-FLEX -2P-050 KIT 10PCS	▶ 4062172179591
TF2000-G1 -827-05	CONN-FLEX -2P-200 KIT 10PCS	▶ 4062172179614
TF2000-G1 -827-05	CORNER-FLEX -4P-003 KIT 10PCS	▶ 4062172179638
TF2000-G1 -827-05	CORNER-FLEX -4P-015 KIT 10PCS	▶ 4062172179676
TF2000-G1 -827-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TF2000-G1 -827-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TF2000-G1 -827-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TF2000-G1 -827-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964

Datablad produktfamilj

TF2000-G1 -827-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TF2000-G1 -830-05	CONN-FLEX -2P-050 KIT 10PCS	▶ 4062172179591
TF2000-G1 -830-05	CONN-FLEX -2P-200 KIT 10PCS	▶ 4062172179614
TF2000-G1 -830-05	CORNER-FLEX -4P-003 KIT 10PCS	▶ 4062172179638
TF2000-G1 -830-05	CORNER-FLEX -4P-015 KIT 10PCS	▶ 4062172179676
TF2000-G1 -830-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TF2000-G1 -830-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TF2000-G1 -830-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TF2000-G1 -830-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TF2000-G1 -830-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TF2000-G1 -840-05	CONN-FLEX -2P-050 KIT 10PCS	▶ 4062172179591
TF2000-G1 -840-05	CONN-FLEX -2P-200 KIT 10PCS	▶ 4062172179614
TF2000-G1 -840-05	CORNER-FLEX -4P-003 KIT 10PCS	▶ 4062172179638
TF2000-G1 -840-05	CORNER-FLEX -4P-015 KIT 10PCS	▶ 4062172179676
TF2000-G1 -840-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TF2000-G1 -840-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TF2000-G1 -840-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TF2000-G1 -840-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TF2000-G1 -840-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TF2000-G1 -865-05	CONN-FLEX -2P-050 KIT 10PCS	▶ 4062172179591
TF2000-G1 -865-05	CONN-FLEX -2P-200 KIT 10PCS	▶ 4062172179614
TF2000-G1 -865-05	CORNER-FLEX -4P-003 KIT 10PCS	▶ 4062172179638
TF2000-G1 -865-05	CORNER-FLEX -4P-015 KIT 10PCS	▶ 4062172179676
TF2000-G1 -865-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TF2000-G1 -865-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TF2000-G1 -865-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TF2000-G1 -865-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TF2000-G1 -865-05	FX -SC08-G2-CT4PJ	▶ 4052899464858
TF2000-G1 -850-05	CONN-FLEX -2P-050 KIT 10PCS	▶ 4062172179591
TF2000-G1 -850-05	CONN-FLEX -2P-200 KIT 10PCS	▶ 4062172179614
TF2000-G1 -850-05	CORNER-FLEX -4P-003 KIT 10PCS	▶ 4062172179638
TF2000-G1 -850-05	CORNER-FLEX -4P-015 KIT 10PCS	▶ 4062172179676
TF2000-G1 -850-05	LTS-SLIMTRACK -2000 KIT 5 PCS	▶ 4062172207300
TF2000-G1 -850-05	FX-QMS-G1 -TU15H6W3-300	▶ 4052899448889
TF2000-G1 -850-05	FX-QMS-G1 -TU16H12W3-300	▶ 4052899448988
TF2000-G1 -850-05	FX-QMS-G1 -TU16H12-300	▶ 4052899448964
TF2000-G1 -850-05	FX -SC08-G2-CT4PJ	▶ 4052899464858

Friskrivningsklausul

Kan ändras utan föregående notifiering. Felaktigheter och försummelse undantagna. Se alltid till att använda den senaste utgåvan.